



Outperforms industrial labellers costing twice as much.

Leave any jobsite looking better than you found it.

Rugged, versatile and packed with time-saving features, the DYMO® Rhino™ 5200 meets all ANSI and TIA/EIA-606-A labelling standards. Time is money, and exclusive one-touch “Hot Keys” save you both on every job. Just press one “Hot Key” to automatically size, space and format text for perfect patch panel labels – then press another to print matching cable flags or face plate tabs, without retyping!

It's just as easy to print module and fixed-length labels, horizontal and vertical wire wraps, terminal and 110 blocks and much more. Print Code 39 and Code 128 barcodes. Access 100+ industry symbols, fractions and punctuation marks with a few quick keystrokes. Add the optional quick-charging lithium-ion battery for uninterrupted productivity.



Hard Case Kit
(see back for details)









DYMO® | Rhino™ 5200 features:

- 1 Meets all ANSI and TIA/EIA-606-A industry labelling standards
- 2 Exclusive one-touch “Hot Keys” automatically size, space and format label text for electrical and patch panels, terminal and 110 blocks, wire and cable flags, horizontal and vertical wraps, vertical and fixed-length applications
- 3 Prints Code 39 and Code 128 barcodes on 19 mm-wide labels – ideal for asset management
- 4 Uses DYMO® Industrial labels with chemical-, heat- and UV-resistant materials; also prints directly on heat-shrink tubes and non-adhesive labels
- 5 Large 14-character, two-line backlit display
- 6 100-Label Memory for storing commonly used labels



Up to

19 mm

IND LABEL APPLICATIONS		LABEL COLOUR	6 mm	9 mm	12 mm	19 mm	24 mm
Labels that stick and stay stuck. DYMO® Industrial labels are tough— jobsite tested and UL recognized. Labels won't smear or fade and are built with industrial-strength adhesives to resist moisture, UV light and extreme temperatures. Whether you are labelling to OSHA, ISO and ANSI colour standards or labelling in harsh conditions, DYMO® Industrial labels have you covered. DYMO® Industrial labels are designed to work exclusively with Rhino™ printers and to perform on a variety of surfaces. LEARN MORE: www.dymo.com/industrial	BLACK ON WHITE	–	18443 <i>S0718580</i>	18444 <i>S0718600</i>	18445 <i>S0718620</i>	1805430	
	BLACK ON YELLOW	–	–	18432 <i>S0718450</i>	18433 <i>S0718470</i>	1805431	
	BLACK ON ORANGE	–	–	18435 <i>S0718490</i>	18436 <i>S0718500</i>	1805427	
	BLACK ON GREY	–	–	1805413	1805419	1805425	
	WHITE ON RED	–	–	1805416	1805422	1805429	
	WHITE ON BLACK	–	1805437	1805435	1805436	1805432	
	WHITE ON GREEN	–	–	1805414	1805420	1805426	
VINYL - UL Recognized Component to UL969 - RoHS compliant 	WHITE ON BLUE	–	–	1805243	1805417	1805423	
	WHITE ON PURPLE	–	–	1805415	1805421	1805428	
	WHITE ON BROWN	–	–	1805412	1805418	1805424	
PERMANENT POLYESTER - UL Recognized Component to UL969 - RoHS compliant 	BLACK ON WHITE	1805442	18482 <i>S0718240</i>	18483 <i>S0718210</i>	18484 <i>S0718220</i>	1734523 <i>S0773830</i>	
	BLACK ON CLEAR	1805440	18508DMO <i>S0718160</i>	622289	622290	1805433	
	BLACK ON METALLIC	1805441	18485 <i>S0718170</i>	18486 <i>S0718180</i>	18487 <i>S0718200</i>	1805434	
HEAT SHRINK TUBES - UL Recognized Component to UL224 - Meets MIL-STD-202G, MIL-M-81531 & SAE-DTL 23053/5 (Class 1 & 3) - RoHS compliant 	BLACK ON WHITE	18051 <i>S0718260</i>	18053 <i>S0718280</i>	18055 <i>S0718300</i>	18057 <i>S0718330</i>	1805443	
	BLACK ON YELLOW	18052 <i>S0718270</i>	18054 <i>S0718290</i>	18056 <i>S0718310</i>	18058 <i>S0718340</i>	1805444	
FLEXIBLE NYLON - UL Recognized Component to UL969 - RoHS compliant 	BLACK ON WHITE	–	–	18488 <i>S0718100</i>	18489 <i>S0718120</i>	1734524 <i>S0773840</i>	
	BLACK ON YELLOW	–	–	18490 <i>S0718080</i>	18491 <i>S0718090</i>	1734525 <i>S0773850</i>	
NON-ADHESIVE TAG - RoHS compliant 	BLACK ON WHITE	18111 <i>S0718350</i>	–	18113 <i>S0718380</i>	–	–	
SELF-LAMINATING - RoHS compliant 	BLACK ON WHITE	–	–	–	–	1734821 <i>S0773860</i>	

Rhino™ 5200 SINGLE UNIT (BOXED)

Code: S0841460

Box includes:

- Rhino™ 5200 printer
- 19 mm white flexible nylon tape
- Quick reference guide
- User manual on CD-rom

Product specifications:

- Runs on optional rechargeable lithium-ion battery pack or 6 AA batteries
- 1 year warranty + 1 year extra when registering
- Unit weight: 900 gr

Optional accessories:

- AC adapter Code: S0721430
- Rechargeable lithium-ion battery pack Code: S0895840
- Hard case Code: S0902390

Rhino™ 5200 HARD CASE KIT

Code: S0841390

Hard Case Kit includes:

- Rhino™ 5200 printer
- User manual on CD-rom
- Quick reference guide
- 19 mm white flexible nylon tape
- 12 mm white vinyl tape
- Rechargeable lithium-ion battery pack
- AC adapter

Product specifications:

- Runs on included lithium-ion rechargeable battery pack with AC adapter or optional 6 AA batteries
- 1 year warranty + 1 year extra when registering
- Unit weight: 2500 gr

For more information or to find out your nearest distributor, please visit www.dymo.com/industrial or call us at +44 (0) 20 7341 5529.



©2011 DYMO®
 DYMO bvba, Industriepark-Noord 30
 B9100 Sint-Niklaas, Belgium
www.dymo.com/industrial