

2 Series MSO

Mixed Signal Oscilloscope Datasheet

*On the Bench or in the Field,
the Oscilloscope that works where you work*



Key performance specifications

Analog input channels

2 or 4 inputs

Bandwidth

70 MHz, 100 MHz, 200 MHz, 350 MHz, and 500 MHz

Sample rate

- 2.5 GS/s half channels
- 1.25 GS/s all channels

Record length

10 M points per channel

Vertical resolution

- 8 bits ADC
- Up to 16 bits in high-resolution mode

Standard trigger types

Edge, pulse width, runt, timeout, logic, setup & hold, rise/ fall time, and parallel bus

Standard analysis

- Cursors: Waveform, V bars, H bars, and V&H bars
- Measurements: 37
- Plots: XY, limit mask
- Math: Basic waveform arithmetic, FFT, and advanced equation editor
- Search: Search on any trigger criteria

Serial trigger, decode and analysis (optional)

I²C, SPI, RS-232/422/485/UART, CAN, CAN FD, LIN, and SENT

Digital input channels (optional)

16 inputs

Arbitrary function generator (optional)

- 50 MHz waveform generation
- Waveform types: Arbitrary, sine, square, pulse, ramp, triangle, DC level, Gaussian, Lorentz, exponential rise/fall, sin(x)/x, random noise, Haversine, and cardiac

Digital pattern generator (optional)

- 4 bit
- User-defined, manual, and toggle

Display

- 10.1-inch TFT color
- WXGA (1280 x 800) resolution
- Capacitive (multi-touch) touchscreen

Connectivity

- USB 2.0 Device (one port)
- USB 2.0 Host (dual-port)
- LAN (10/100 MB/s Base-T Ethernet)

Battery pack (optional)

- Battery pack with 2 battery slots and hot-swap capability
- Typical usage is 8 hours with dual batteries

Remote control

Remotely view and control the oscilloscope over a network connection through remote Virtual Network Computing (VNC)

VESA mount

100 mm x 100 mm VESA interface

Security

Kensington lock: T-Bar style

Standard probes

One TPP0200 200 MHz, 10:1 voltage probe per channel

Collaborative tools (optional)

- TekDrive: Save and recall waveforms, setups, and screenshots from TekDrive cloud. Share data with other members on the team.
- TekScope: Perform basic instrument control and transfer waveform data to your PC. Offline analysis; such as protocol decode, and automated measurements on saved data.


Accessories (optional)

- Protective case bundle: Carrying bag, kick stand, protective rubber case
- Rackmount kit
- Hard case
- Battery charger

Warranty

One year standard

Tektronix next generation oscilloscopes



2 Series MSO	3 Series MDO	4 Series MSO	5 Series B MSO	6 Series B MSO
Compact, portable, battery-operated instrument	Extreme versatility for any bench	Up to 6 channels of high-visibility bench test	Advanced analysis and up to 8 inputs	Unmatched detail on high-speed signals



Compact, versatile oscilloscope for daily debug

The 2 Series MSO features up to 4 analog channels, 500 MHz bandwidth, 2.5 GS/s sample rate, 16 channel MSO, 50 MHz AFG, 4-bit digital pattern generator, advanced triggers, and protocol decode, all in a compact form factor about 1.5" thick. The 2 Series MSO is the go-to oscilloscope for electronic debug and test, no matter where you work.

With a capacitive touchscreen and a highly intuitive user interface truly designed for touch, the 2 Series MSO is a member of the Tektronix family of award-winning next generation oscilloscopes. The shared user and programmatic interface provides a seamless experience between all Tektronix next generation oscilloscopes.

The optional battery pack enables you to use the same instrument in the lab and in the field.

A large catalog of compatible probes and well-rounded set of accessories make the 2 Series MSO the most capable and versatile instrument in its class and suitable for a variety of applications.

Intuitive touchscreen with simplified front panel

The 2 Series MSO offers the same, award-winning user interface as the higher-end Tektronix oscilloscopes and supports the touch interactions that you have come to expect in a touch-enabled consumer device.

- Drag waveforms to adjust horizontal and vertical position or to pan a zoomed view.
- Pinch and expand to change scale or zoom in/out in either horizontal or vertical directions.
- Swipe in from the right to reveal the results bar or down from the top to access the menus in the upper left corner of the display.



Interact with the capacitive touch display.

The simplified front panel retains critical buttons and knobs with color-coded LED ring lights, allowing quick access and easy adjustment of the most frequently-used instrument settings.

The membrane switch technology makes it rugged and suitable for use in harsh environments and easy to clean.



Simplified and intuitive front panel with color coded LEDs.

The combination of a streamlined front panel with an intuitive touch interface help any new engineer to self-discover and begin using the instrument.

A USB mouse and keyboard can be used as a third interaction method with the instrument.



Simultaneously view analog channels, decoded serial bus waveform, results table, measurement results, math FFT plot, and cursor readouts along with the setup information for each input with the highly customizable user interface.

Exceptionally easy to use interface with comprehensive analysis for fast insight

The user interface on the 2 Series MSO is designed from the ground up for touch operation. All the key information is presented as a series of badges with visual cues to show association. Get immediate access to instrument configuration or waveform management tasks with a single tap.

The 2 Series MSO offers a revolutionary new stacked display mode. Traditionally all the waveforms were overlaid on a single graticule leading to unwanted tradeoffs:

- The vertical scale and position of each waveform needs to be adjusted so that they do not overlap. This results in usage of only a small percentage of the ADC range leading to inaccurate measurements.
- Adjusting the waveform vertical scale and position leads to overlap, making it difficult to distinguish details on an individual waveform.

In stacked display mode, each waveform gets its own slice (additional graticule) representing the full ADC range to enable maximum visibility and accuracy. Groups of channels can also be overlaid to enable visual comparison of signals.


The 2 Series MSO offers a comprehensive set of standard analysis tools including:

- Waveform and screen-based cursors with selectable readout location.
- 37 automated measurements with measurement statistics and gating, the ability to add an unlimited number of measurements, go from one occurrence to the next, and immediate viewing of the minimum or maximum result.
- Basic and advanced waveform math including arbitrary equation editing.
- Basic FFT analysis with options to view magnitude or phase, multiple options to customize window type, gating, and units.

The large display in the 2 Series MSO provides plenty of viewing area not only for signals, but also for plots, measurement results tables, bus decode tables, and more. You can easily resize and relocate the various views to suit your needs.

Triggering


Discovering a device fault is only the first step. Next, you must capture the event of interest to identify root cause. The 2 Series MSO provides a complete set of advanced triggers, including runt, logic, pulse width, triggers, timeout, rise/fall time, setup and hold, serial packet, and parallel data used to capture complex infrequent events.



Configuration menus are accessed by simply double tapping on the item of interest. In this case the trigger badge was tapped to open the trigger menu.

Act on Event

The Act on Event capability built into the instrument enables you to setup the oscilloscope to respond by performing certain actions when a specified condition such as a trigger event, measurement limit failure, search event, or mask test events occur. This supports the capture and analysis of rarely occurring events.



An oscilloscope can be automated using the Act on Event feature when a specified condition occurs.

Navigation and search

With up to 10 M point record length, you can capture many events of interest, thousands of serial packets in a single acquisition, while maintaining high resolution to zoom in on fine signal details.


Finding events of interest in a long waveform record can be time consuming without the right search tools.

The search feature allows you to automatically search through your acquisition for user-defined events. All occurrences of the event are highlighted with search marks for easy navigation. Search types include edge, pulse width, timeout, runt, window, logic, setup and hold, rise/fall time, and parallel/serial bus packet content. You can also quickly jump to the minimum and maximum value of search results.

Callouts

Documenting test results and methods are critical when sharing data across a team, recreating a measurement later, or delivering a customer report.

With a few taps on the screen, create as many custom callouts as needed to document the specific details on the waveforms. With each callout, you can customize the text, location, color, font size, and font.



Example of pulse width trigger used to trigger on a narrow pulse.



A bus waveform provides time-correlated decoded packets while the bus decode table presents all the packets from the entire acquisition. Search can be used to navigate.

Mask testing

Mask testing offers a way to test the quality of a signal. A mask defines a portion of the oscilloscope display that a signal must not enter. A mask can be defined based on a golden signal with user-defined tolerances or drawing mask segments on the screen.

The 2 Series MSO provides a comprehensive set of mask tools that:

- Define test duration in number of waveforms.
- Set a violation threshold that must be met before considering a test failure.
- Count violations/failures and reporting statistical information.
- Set actions upon violations, test failure, and test complete.



Limit mask test based on golden reference signal


Serial protocol triggering and analysis (optional)

The 2 Series MSO offers a robust set of tools for working with the most common serial buses found in embedded design including; I2C, SPI, RS-232/422/485/UART, CAN, CAN FD, LIN, and SENT.

The protocol decode and triggering capability is invaluable to trace the flow of activity through a system by observing the traffic on one or more serial buses.

- Serial protocol triggering allows you trigger on specific packet content including; start of packet, specific addresses, specific data content, unique identifiers, and errors.
- Bus waveforms provide a higher-level, combined view of the individual signals of your bus such as; clock, data, and chip enable. This makes it easy to identify where packets begin and end, and identifying sub-packet components such as; address, data, identifier, and CRC.
- The bus waveform is time-aligned with all other displayed signals, making it easy to measure timing relationships across various parts of the system under test.
- The bus decode table provides a tabular view of all decoded packets in an acquisition. Packets are timestamped and listed

consecutively with columns for each component like address and data.




Bus menu provides options to configure the bus parameters.

Digital channels (optional)

The 2 Series MSO comes equipped with 16 digital channels. A P6316 logic probe can be used to connect up to 16 signals to the digital inputs of the oscilloscope. The accessories that are included with the probe enable you to connect directly to 8 x 2 square pin headers. The included flying lead sets and grabbers allow you to clip into surface mount devices or test points offering additional flexibility.

Each digital channel can be viewed separately to see its state. Alternately, several digital channels can be grouped to view them in a bus form. Symbol tables can also be applied to the bus view to get a higher level view of the bus transactions. Pattern triggering capability can be used to trigger on a pattern of interest.




Digital channel trigger and decode

Arbitrary function generator (optional)

The 2 Series MSO includes an optional 50 MHz arbitrary function generator (AFG) for simulating sensor signals within a design or adding noise to signals to perform margin testing. The AFG output is multiplexed with the Aux out signal.

Several predefined waveforms including sine, square, pulse, ramp/triangle, DC, noise, sin(x)/x (Sinc), Gaussian, Lorentz, exponential rise/fall, Haversine, and cardiac are included.


The AFG provides 128k points of record for loading waveforms captured on the analog input, a saved file. Alternatively, Tektronix ArbExpress PC-based waveform creation and editing software can be used to create complex waveforms quickly and easily.



Flexible settings of AFG outputs. In this test case, 25% of noise was added to the Sine.

Frequency response analysis (Bode plot)


Analyze the frequency response of a system using the built-in Bode plot feature. The input voltage is swept across the user-selected range using the internal AFG or a supported external AFG. The gain and phase of the output relative to the input voltage is plotted at each point.



Digital pattern generator (optional)

A 4-bit digital pattern generator with 4k point record length per bit is included on the 2 Series MSO for generating 4 digital signals at predefined voltage levels.

An output pattern can be loaded in memory using a predefined CSV file or the state of each output can be manually set to high, low, toggle, or Hi-Z as needed.



Digital pattern generator

Connectivity

The 2 Series MSO has several ports for you to connect the instrument to a network, directly to a PC, or to other test equipment.

- Two USB 2.0 ports enable easy transfer of screenshots, instrument settings, and waveform data to a USB mass storage device. A USB mouse and keyboard can also be attached to USB host ports for instrument control and data entry.
- The USB device port allows you to control the oscilloscope remotely from a PC.
- The standard 10/100BASE-T Ethernet port enables easy connection to networks, and remotely controlling the instrument and viewing the acquired data.

Programmable interface and backward compatibility

Programmable interface commands are used to remotely control the instrument through the USB device port or the Ethernet port. This allows you to program the instrument to perform an automated set of tasks or integrate into a larger system with other equipment for performing specific tasks.

The programmable interface command set is compatible with the next generation of Tektronix oscilloscopes, making it easy to reuse code written for other Tektronix oscilloscopes.

The instrument supports a compatibility mode that, when enabled, makes the 2 Series MSO compatible with the programmable commands of the TDS2000, TBS1000, and MSO/DPO2000 family of Tektronix oscilloscopes. Compatibility mode simplifies the replacement of an older model oscilloscope in an existing test system with the 2 Series MSO.

Battery pack (optional)

The 2 Series MSO supports an optional battery pack that provides additional flexibility to perform measurements in areas where there is no AC power available such as testing equipment in the field.

The battery pack has two battery slots and allows for hot swapping of the batteries during operation to extend run time.

The batteries are charged when the instrument is on AC power, or using an external charger.



Battery pack with two battery slots can be mounted on the back of the instrument.



External battery charger

Accessories


In addition to the battery pack, several other accessories are available for the 2 Series MSO:

- Install the instrument in a rack for production with the rackmount kit.
- Carry the instrument into the field using the protective case bundle. The bundle includes a carrying bag, protective rubber case, and kick stand
- Ship the instrument using the hard travel case

The 100 mm x 100 mm standard VESA interface on the back of the instrument is compatible with a wide variety of accessories.



MSO24 mounted on an off the shelf arm



Rackmount kit



Bundle with carrying bag, kick stand, and protective case



Hard carrying case

TekDrive

The 2 Series MSO is natively integrated with TekDrive collaborative test and measurement data workspace. TekDrive allows you to upload, store, organize, search, download, and share any file type from any connected device.

- Seamlessly access your data anywhere
- Save/recall directly on instruments
- Inspect, analyze, and report saved data on any device using a browser
- Collaborate seamlessly with other contributors
- Integrate into any workflow with scripting using REST API



TekScope PC analysis software

Get the analysis capability of an award-winning oscilloscope on your PC. Analyze waveforms anywhere, anytime.

- Analyze waveforms anywhere without an oscilloscope, using the same interface as the oscilloscope
- Share data with colleagues and customers
- Synchronize waveforms from multiple oscilloscopes on the same screen
- Add advanced analysis capabilities such as; spectrum analysis, jitter analysis, and advanced bus decoding



TekScope software on a PC

Kickstart

The 2 Series MSO is compatible with Kickstart Software. Kickstart is a PC-based application that enables setup and data collection across many types of bench instruments. It also offers a set of tools for quick and easy interaction and analysis of data.

- Connect and control up to 8 instruments simultaneously
- Supports SMU, DMM, power supplies, oscilloscopes, AFG, data loggers, and sensitive instruments
- Automate data collection
- Save and replicate test configurations
- Plot collected data for a visual inspection of trends
- Export data in different formats




Kickstart multi-instrument controls and analysis

Education features

Help when and where you need it

The 2 Series MSO includes several resources to help get answers to your questions rapidly:

- Graphics and explanatory text in menus provide quick feature overviews.
- All menus include a question mark icon in the upper right corner. Tapping the icon opens the section of the integrated help system that applies to menu you are in.
- The *Getting acquainted with your instrument* section in the Help menu enables you to quickly come up to speed with the instrument in a few minutes.



Get answers to your questions using the integrated help.

Feature control

The 2 Series MSO enables educators to devote more time to teaching circuit concepts instead of lab setup and management.

Educators can disable autoset, cursors, and automated measurements on the instruments. This allows students to focus on the basic concepts and helps them understand how to use the horizontal and vertical controls to get the waveform display, use the graticule to measure time and voltage, and manually plot/calculate the signal characteristics.

Specifications

All specifications are typical unless noted otherwise. All specifications apply to all models unless noted otherwise.

Analog signal acquisition system

Analog input channels	MSO22: 2 channel MSO24: 4 channel						
Input coupling	AC, DC						
Input impedance							
BNC	1 M Ω \pm 1%, 14 pF \pm 3 pF						
TPP0200 probe tip	10 M Ω , < 12 pF						
P6139B probe tip	10 M Ω , < 8 pF						
Sensitivity range (coarse), 1 MΩ	1 mV/Div to 10 V/Div in a 1-2-5 sequence						
Sensitivity range (fine)	Continuous adjustment from 1 mV/DIV to 10 V/DIV, 1 M Ω 1x						
Sensitivity resolution (fine)	\leq 10% of current setting						
Vertical resolution	8 bit						
Maximum input voltage, 1 MΩ DC-coupled	Maximum input voltage at the BNC, 300 V _{rms} . Installation category II Derate at 20 dB/decade between 4.5 MHz to 45 MHz Derate at 14 dB between 45 MHz to 450 MHz; above 450 MHz, 5 V _{rms} Maximum peak input voltage at the BNC: \pm 424 V						
DC gain accuracy	Guaranteed for 2 mV/div and above, typical otherwise. Specification valid after 30 minute warm-up and Signal Path Compensation (SPC) at ambient. <2 mV/div: \pm 3.0%, typical, derated at 0.100%/°C above 30 °C \geq 2 mV/div: \pm 2.0%, derated at 0.100%/°C above 30 °C						
Offset ranges	1 mV/div to 63.8 mV/div : \pm 1 V 63.9 mV/div to 999.5 mV/div : \pm 10 V 1 V/div to 10 V/div : \pm 100 V						
Bandwidth selections	20 MHz, 70 MHz, 100 MHz, 200 MHz, 350 MHz, and 500 MHz (when equal to or less than instrument's rated bandwidth)						
Analog channel bandwidth	70 MHz, 100 MHz, 200 MHz, 350 MHz, and 500 MHz. 500 MHz bandwidth guaranteed from 4 mV/div to 10 V/div.						
Deskew range	-95 ns to +95 ns						
Crosstalk (channel isolation)	<table border="1"> <thead> <tr> <th></th> <th>\leq 100 MHz</th> <th>> 100 MHz</th> </tr> </thead> <tbody> <tr> <td>1 MΩ</td> <td>100:1</td> <td>30:1</td> </tr> </tbody> </table>		\leq 100 MHz	> 100 MHz	1 M Ω	100:1	30:1
	\leq 100 MHz	> 100 MHz					
1 M Ω	100:1	30:1					
Sample rate range	Maximum 1.25 GS/s - All channels Maximum 2.5 GS/s - Half channel						
Record length range	10 M Standard						
Seconds/Division range	1 ns/div to 1000 s/div when in half channel mode 2 ns/div to 1000 s/div when in full channel mode						
Timebase accuracy	\pm 25 x 10 ⁻⁶ over any over any \geq 1 ms interval Guaranteed, the specification valid after 30 minute warm-up and Signal Path Compensation (SPC) at ambient.						

Timebase delay time range -10 divisions to 5000 s

Triggering system

Edge-type trigger sensitivity, DC-coupled	The greater of 2 mV or 0.4 div from DC to 20 MHz The greater of 3 mV or 0.5 div from >20 MHz to 70 MHz The greater of 4 mV or 0.5 div from >70 MHz to 100 MHz The greater of 4 mV or 0.6 div from >100 MHz to 200 MHz The greater of 5 mV or 0.7 div from >200 MHz to 350 MHz The greater of 6 mV or 0.8 div from >350 MHz to instrument bandwidth
Trigger modes	Auto, normal, and single
Trigger coupling	DC, HF Reject (attenuates > 50 kHz), LF Reject (attenuates < 50 kHz), noise reject (reduces sensitivity)
Trigger level ranges	
Any input channel	±5 divisions from center of screen
Aux In	±8 V
Trigger types	
Edge	Positive, negative, or either slope on any channel.
Pulse Width	Trigger on width of positive or negative pulses. Event can be time- or logic-qualified.
Timeout	Trigger on an event which remains high, low, or either, for a specified time period. Event can be logic-qualified.
Runt	Trigger on a pulse that crosses one threshold but fails to cross a second threshold before crossing the first again. Event can be time- or logic-qualified.
Logic	Trigger when logic pattern goes true, goes false, or occurs coincident with a clock edge. Pattern (AND, OR, NAND, NOR) specified for all input channels defined as high, low, or don't care. Logic pattern going true can be time-qualified.
Setup/Hold	Trigger on violations of both setup time and hold time between clock and data present on any input channels.
Rise/Fall	Trigger on pulse edge rates that are faster or slower than specified. Slope may be positive, negative, or either. Event can be logic-qualified.
Parallel (with MSO option)	Trigger on a parallel bus data value. Parallel bus can be from 1 to 20 bits (from the digital and analog channels) in size. Supports binary and hex radices.
I2C (option)	Trigger on start, repeated start, stop, missing ack, address (7 or 10 bit), data, or address and data on I2C buses up to 10 Mb/s.
SPI (option)	Trigger on slave select, idle time, or data (1-16 words) on SPI buses up to 20 Mb/s.
RS-232/422/485/UART (option)	Trigger on start bit, end of packet, data, and parity error up to 15 Mb/s.
CAN (option)	Trigger on start of frame, type of frame (data, remote, error, or overload), identifier, data, identifier and data, end of frame, missing ack, and bit stuff error on CAN buses up to 1 Mb/s and CAN-FD buses up to 16 Mb/s.
LIN (option)	Trigger on sync, identifier, data, identifier and data, wakeup frame, sleep frame, and error on lin buses up to 1 Mb/s.
SENT (option)	Trigger on start of packet, fast channel status and data, slow channel message ID and data, and CRC errors.
Trigger holdoff range	0 s minimum to 10 s maximum. Hold off may not function correctly in sequence trigger mode.

Digital channel acquisition

Digital input channels	16 Digital Inputs [D0:D15]
Input resistance, typical	101 K Ω to ground
Input capacitance, typical	8 pF Specified at the input to the P6316 probe with all 8 ground inputs connected to the user's ground. Use of leadsets, grabber clips, ground extenders, or other connection accessories may compromise this specification.
Minimum input signal swing, typical	500mV peak-to-peak Specified at the input to the P6316 probe with all 8 ground inputs connected to the user's ground. Use of leadsets, grabber clips, ground extenders, or other connection accessories may compromise this specification.
Maximum input signal swing, typical	+30 V, -20 V
Thresholds	Thresholds per set of 8 channels
Threshold Selections	TTL, CMOS, ECL, PECL, User-Defined
Threshold voltage range	-15 V to +25 V
Vertical resolution	1 bit
Threshold accuracy	\pm [180 mV + 2% of threshold setting after calibration]. Requires valid SPC.
Minimum detectable pulse	2.0 ns Specified at the input to the P6316 probe with all eight ground inputs connected to the user's ground. Use of lead sets, grabber clips, ground extenders, or other connection accessories may compromise this specification.

Acquisition system modes

Sample	Acquired sample values
Peak Detect	Highest and the lowest sample within the decimation interval
Averaging	Average of a series of acquired waveforms up to 10,240 acquisitions
Envelope	Min-Max envelope over multiple acquisitions
Hi-Res	Applies a unique bandwidth filter for each sample rate that maintains the maximum bandwidth possible for that sample rate while preventing aliasing and removing noise from the oscilloscope amplifiers and ADC above the usable bandwidth for the selected sample rate.
Roll Mode	Scrolls sequential waveform points across the display in a right-to-left rolling motion, at timebase speeds of 40 ms/div and slower, when in Auto trigger mode.

Waveform measurements

Cursors	Waveform, V bars, H bars, and V&H bars
Automatic measurements	37, of which an unlimited number can be displayed as either individual measurement badges or collectively in a measurement results table
Amplitude measurements	Amplitude, maximum, minimum, peak-to-peak, positive overshoot, negative overshoot, mean, RMS, AC RMS, top, base, and area
Time measurements	Period, frequency, unit interval, data rate, positive pulse width, negative pulse width, skew, delay, rise time, fall time, phase, rising slew rate, falling slew rate, burst width, positive duty cycle, negative duty cycle, time outside level, setup time, hold time, duration n-periods, high time, and low time, time to max, and time to min
Measurement statistics	Mean, standard deviation, maximum, minimum, and population. Statistics are available on both the current acquisition and all acquisitions

Reference levels User-definable reference levels for automatic measurements can be specified in either percent or units. Reference levels can be set to global for all measurements, per source channel or signal, or unique for each measurement

Waveform math

Arithmetic Add, subtract, multiply, and divide

Math Functions Integrate, differentiate, log 10, log e, square root, exponential, and abs

Relational Boolean result of comparison >, <, ≥, ≤, =, and ≠

Logic AND, OR, NAND, NOR, XOR, and EQV

FFT Spectral magnitude and phase, and real and imaginary spectra

FFT units Magnitude: linear and log (dBm)
Phase: degrees, radians, and group delay

FFT window functions Hanning, rectangular, hamming, blackman-harris, flattop2, gaussian, kaiser-bessel, and tekexp

Search

Search Types Search through long records to find all occurrences of user specified criteria including edges, pulse widths, timeouts, runt pulses, logic patterns, setup & hold violations, rise/fall times, and bus protocol events.

Search results Waveform view, results table.

Arbitrary function generator

AFG outputs 1 (Multiplexed with Aux Out)

Operating modes Continuous, burst

Function types Arbitrary, sine, square, pulse, ramp, DC level, Gaussian, Lorentz, exponential rise/fall, sin(x)/x, random noise, Haversine, and Cardiac.

Amplitude and frequency range Values are peak-to-peak voltages.

Waveform	Amplitude range 50 Ω	Amplitude range 1 MΩ	Frequency range
Arbitrary	10 mV to 2.5 V	20 mV to 5 V	0.1 Hz to 25 MHz
Sine	10 mV to 2.5 V	20 mV to 5 V	0.1 Hz to 50 MHz
Square	10 mV to 2.5 V	20 mV to 5 V	0.1 Hz to 20 MHz
Pulse	10 mV to 2.5 V	20 mV to 5 V	0.1 Hz to 20 MHz
Ramp	10 mV to 2.5 V	20 mV to 5 V	0.1 Hz to 500 KHz
DC Level		20 mV to 5V	
Gaussian	10 mV to 1.25 V	20 mV to 2.5 V	0.1 Hz to 5 MHz
Lorentz	10 mV to 1.2 V	20 mV to 2.4 V	0.1 Hz to 5 MHz
Exponential rise	10 mV to 1.25 V	20 mV to 2.5 V	0.1 Hz to 5 MHz
Exponential decay	10 mV to 1.25 V	20 mV to 2.5 V	0.1 Hz to 5 MHz
Sin(X)/X	10 mV to 1.5 V	20 mV to 3.0 V	0.1 Hz to 2 MHz
Random noise	10 mV to 2.5 V	20 mV to 5 V	
Haversine	10 mV to 1.25 V	20 mV to 2.5 V	0.1 Hz to 5 MHz
Table continued...			

Waveform	Amplitude range 50 Ω	Amplitude range 1 M Ω	Frequency range
Cardiac	10 mV to 2.5 V	20 mV to 5 V	0.1 Hz to 500 KHz

Ramp and triangle waveform

DC offset Range	± 2.5 V into Hi-Z ± 1.25 V into 50 Ω
DC offset Resolution	500 μ V (50 Ω) 1 mV (Hi-Z)
DC offset accuracy	\pm [(1.5% of absolute offset voltage setting) + 1 mV] Add 3 mV of uncertainty per 10 $^{\circ}$ C change from 25 $^{\circ}$ C ambient Guaranteed, specification valid after 30 minute warm-up and Signal Path Compensation (SPC) at ambient.

Digital pattern generator

Channels	4
Pattern memory length	4 K bits
Output amplitude	2.5 V, 3.3 V, 5 V (Continuous Mode) 5 V (Burst Mode)
Bit Rate	1 bps to 25 Mbps

Display system

Display type	Display area – 217 mm x 135 mm, TFT active matrix, and Liquid Crystal Display (LCD) with capacitive touch.
Display resolution	1,280 horizontal \times 800 vertical pixels
Display modes	Overlay and stacked
Luminance	260 cd/m ² Display luminance is specified for a new display set at full white brightness.
Color support	16,777,216 (8-bit RGB) colors
Zoom	Horizontal and vertical zooming is supported in all waveform and plot views
Interpolation	Sin(x)/x and linear
Waveform styles	Vectors, dots, variable persistence, and infinite persistence
Graticules	Movable and fixed graticules, selectable between grid, time, full, and none
Color palettes	Normal and inverted for screen captures Individual waveform colors are user-selectable
Format	YT, XY
Language support	English, Japanese, Simplified Chinese, Traditional Chinese, French, German, Italian, Spanish, Portuguese, Russian, Korean

Interfaces, input, and output ports

USB interface	Two USB 2.0 high speed host ports on the side of the instrument One USB 2.0 high speed device port on the side of the instrument (USBTMC support)
Ethernet Interface	One 8-pin RJ-45 connector that supports 10/100 Mb/s and 1000 Mbps Ethernet (in full duplex mode only)

Probe compensator, output voltage and frequency

Characteristic	Value
Output voltage	Normal: 0-2.5 V amplitude
Source impedance	Normal: 1 k Ω
Frequency	1 kHz

Auxiliary output (Aux out)**Aux out connector and functional modes**

A single BNC connector
 Acquisition (main) trigger out and AFG out
 Output can be configured to provide a positive or negative pulse when oscilloscope triggers

Aux out output voltage

Non-AFG voltage thresholds are listed in the following table:

Characteristic	Limits
V_{out} (HI)	≥ 2.5 V open circuit; ≥ 1.0 V into a 50 Ω load to ground
V_{out} (LO)	≤ 0.7 V into a load of ≤ 4 mA; ≤ 0.25 V into a 50 Ω load to ground

Aux input

300 Vrms CAT II with peaks $\leq \pm 425$ V

Security lock

Rear-panel security slot connects to standard Kensington-style lock

VESA mount

Standard (VESA MIS-D 100) 100 mm x 100 mm VESA mounting points on rear of instrument

Ground lug

Provides a safe ground return path when the instrument is operating on battery

Software

VNC	Remotely control and view the screen on the instrument
IVI Driver	Provides a standard instrument programming interface for common applications such as LabVIEW, LabWindows/CVI, Microsoft .NET, and MATLAB. Compatible with python, C/C++/C# and many other languages through VISA.
TekScope	TekScope brings the power of the oscilloscope analysis environment to the PC. You can have the flexibility to perform analysis tasks including serial decode, power analysis, timing, eye, and jitter analysis outside the lab. Visit tek.com/software/tekscope-pc-analysis-software to learn more.
TekDrive	Upload, store, organize, search, download, and share any file type from any connected device. TekDrive is natively integrated into the 2 Series MSO for seamless sharing and recalling of files. No USB stick is required. Visit tek.com/software/tekdrive to learn more.
Programming examples	Programming with the 2/4/5/6 Series platforms has never been easier. With a programmers manual and a GitHub site you have many commands and examples to help you get started remotely automating your instrument. Visit github.com/TEKTRONIX/PROGRAMMATIC-CONTROL-EXAMPLES

Power supply system

Power consumption	60 W maximum
Source voltage	100 – 240 VAC \pm 10% (50/60 Hz)
AC Adapter output	24 V DC, 2.71 A

Battery

Description	Requires Opt 2-BATPK or 2-BP battery pack, with 2 slots for batteries Supports up to 2 TEKBAT-01 Li-Ion rechargeable batteries
Cell chemistry	Li-Ion
Nominal capacity	6700 mAh
Voltage	14.52 VDC
Weight	450 g (1 lb)
Battery operating time, typical	Up to 4 hours with single battery Up to 8 hours with dual batteries Hot swappable

Mechanical characteristics

Weight

Instrument only	1.8 kg (4 lbs)
Instrument with battery pack	3.2 kg (7 lbs) – one battery 3.6 kg (8 lbs) – two batteries

Instrument only dimensions

Height	210 mm (8.26 in)
Width	344 mm (13.54 in)
Depth	40.4 mm (1.59 in)

Instrument with battery pack dimensions

Height	210 mm (8.26 in)
Width	344 mm (13.54 in)
Depth	78 mm (3.07 in)

Clearance requirements The clearance requirement for adequate cooling is 13 mm (0.5 in) on the rear of the instrument along the bottom edge (inlet vents) and top edge (exhaust vents).

Rackmount configuration 5U

Environmental

Temperature

Operating	0 °C to +50 °C (+32 °F to 120 °F)
Operating battery	0 °C to 45 °C (+32 °F to 113 °F)
Non-operating	-20 °C to +60 °C (-4 °F to 140 °F)

Humidity

Operating	5% to 90% relative humidity at temperatures up to +30 °C, 5% to 60% relative humidity at temperatures greater than +30 °C and up to +50 °C
Non-operating	5% to 90% relative humidity at temperatures up to +30 °C 5% to 60% relative humidity at temperatures greater than +30 °C and up to +60 °C

Altitude

Operating	Up to 3,000 meters (9,842 feet)
Non-operating	Up to 12,000 meters (39,370 feet)

Regulatory

CE marked for the European Union and UL approved for the USA and Canada
RoHS compliant

Ordering information

Use the following steps to select the appropriate instrument and options for your measurement needs.

Step 1 – Select the instrument model

Model	Description
MSO22	Mixed Signal Oscilloscope: 2 analog channels, 2.5 GS/s sample rate, 10 Mpts record length
MSO24	Mixed Signal Oscilloscope: 4 analog channels, 2.5 GS/s sample rate, 10 Mpts record length

Each model includes the following:

- TPP0200 200 MHz, 10:1 probe (one per channel)
- Instrument stand
- Installation and safety manual (translated in English, Japanese, and Simplified Chinese)
- Embedded help
- External power supply
- Calibration certificate documenting traceability to National Metrology Institute(s) and ISO9001/ISO17025 quality system registration
- One-year warranty covering all parts and labor cost on the instrument. One-year warranty covering all parts and labor cost on included probes

Step 2 – Configure bandwidth (required)

Configure your oscilloscope by selecting the analog channel bandwidth you need. You can also upgrade the bandwidth later by purchasing an upgrade option.

Bandwidth option	Bandwidth range
2-BW-70	70 MHz
2-BW-100	100 MHz
2-BW-200	200 MHz
2-BW-350	350 MHz
2-BW-500	500 MHz

Step 3 – Add functionality

Order additional items with your instrument.

Option	Description
2-P6139B	Add 500 MHz, 10x probes (one per channel). This is the recommended option for 350 MHz or 500 MHz bandwidth instruments.
2-BATPK	Battery pack with 2 battery slots and 1 battery (ships with instrument) for use with the 2 Series MSO.

Step 4 – Add instrument software functionality with an option bundle

Choose from option bundles with different levels of functionality to suit your application needs.

Feature	Description
2-MSO	Add MSO function with 16 digital channels; includes P6316 digital probe and accessories
2-SOURCE	Arbitrary function generator (AFG), digital pattern generator (DPG), and frequency response analysis (Bode plot)

Table continued...

Feature	Description
2-SERIAL	I ² C, SPI, UART, CAN, CAN-FD, SENT, LIN serial trigger and analysis
2-ULTIMATE	Includes 2-SOURCE and 2-SERIAL

Step 5 – Add additional probes and adapters

Add additional recommended probes and adapters

Passive voltage probes	Description
TPP0100	100 MHz bandwidth, 10x attenuation, BNC interface
TPP0200	200 MHz bandwidth, 10x attenuation, BNC interface
P2221	6 MHz to 200 MHz bandwidth, 1x / 10x attenuation, BNC interface
P6139B	500 MHz bandwidth, 10x attenuation, BNC interface
P6101B	15 MHz bandwidth, 1x attenuation, BNC interface
P3010	100 MHz bandwidth, 10x attenuation, BNC interface

Current probes	Description
TCPA300	Current probe amplifier
With TCP312A	DC to 100 MHz, 1 mA
With TCP305A	DC to 50 MHz, 5 mA
With TCP303	DC to 15 MHz, 5 mA
TCPA400	Current probe amplifier
With TCP404XL	DC to 2 MHz, 1 A
TCP2020	DC to 50 MHz, 10 mA
A622	DC to 100 KHz
P6021A	120 Hz to 60 MHz, 2 mA/mV, 10 mA/mV
P6022	935 Hz to 120 MHz, 1 mA/mV, 10 mA/mV
TRCP3000	1 Hz to 16 MHz, 2 mV/A
TRCP0600	12 Hz to 30 MHz, 10 mV/A
TRCP0300	9 Hz to 30 MHz, 20 mV/A
CT1	25 KHz to 1 GHz, 5 mV/mA
CT2	1.2 KHz to 200 MHz, 5 mV/mA
CT6	250 KHz to 2 GHz, 5 mV/mA

High voltage single ended probe	Description
P5100A	500 MHz bandwidth, 100x attenuation
P6015A	75 MHz bandwidth, 1000x attenuation
P5122	200 MHz bandwidth, 100x attenuation
P5150	500 MHz bandwidth, 50x attenuation

High voltage differential probe	Description
P5200A	50 MHz bandwidth, 50:1/500:1 attenuation

Digital logic probe	Description
P6316	16 channel digital probe for MSO functionality

Step 6 – Select accessories

Add additional recommended accessories.

Optional accessories	Description
2-BP	Battery pack with 2 battery slots and 1 battery for use with 2 Series MSO (ships separately)
TEKBAT-01	Additional battery for use with battery pack 2-BP or Opt 2-BATPK
TEKCHG-01	Standalone battery charger for charging TEKBAT-01 battery
2-RK	Rackmount kit
2-PC	Carrying bag with kickstand and protective case for instrument
2-HC	Hard carrying case
119-9125-XX	Additional AC/DC power supply
065-1088-XX	Additional 2 Series MSO stand

Step 7 – Select power cord option

Optional accessories	Description
A0	North America power plug (115 V, 60 Hz)
A1	Universal Euro power plug (220 V, 50 Hz)
A2	United Kingdom power plug (240 V, 50 Hz)
A3	Australia power plug (240 V, 50 Hz)
A5	Switzerland power plug (220 V, 50 Hz)
A6	Japan power plug (100 V, 50/60 Hz)
A10	China power plug (50 Hz)
A11	India power plug (50 Hz)
A12	Brazil (60 Hz)
A99	No power cord
E1	Universal euro bundle

Step 8 – Select service options

Protect your investment and your uptime with a service package for your 2 Series MSO.

Optimize the lifetime value of your purchase and lower your total cost of ownership with a calibration and extended warranty plan for your 2 Series MSO. Plans range from standard warranty extensions covering parts, labor, and 2-day shipping to Total Product Protection with repair or replacement coverage from wear and tear, accidental damage, ESD or EOS. See the following table for specific service options available on the 2 Series MSO family of products. Compare factory service plans at tek.com/en/services/factory-service-plans.

Additionally, Tektronix is a leading accredited calibration services provider for all brands of electronic test and measurement equipment, servicing more than 140,000 models from 9,000 manufacturers. With 100+ labs worldwide, Tektronix serves as a global partner, delivering tailored whole-site calibration programs with OEM quality at a market price. View whole-site calibration service capabilities at tek.com/en/services/calibration-services.

Service options	Description
R3	Standard warranty extended to 3 years. Covers parts, labor cost, and 2-day shipping within country. Guarantees faster repair time than without coverage. All repairs include calibration and updates. Hassle free - a single call starts the process
R5	Standard warranty extended to 5 years. Covers parts, labor cost, and 2-day shipping within country. Guarantees faster repair time than without coverage. All repairs include calibration and updates. Hassle free - a single call starts the process
T3	Three year total protection plan, includes repair or replacement coverage from wear and tear, accidental damage, ESD or EOS plus preventative maintenance. Including a 5 day turnaround time and priority access to customer support
T5	Five year total protection plan, includes repair or replacement coverage from wear and tear, accidental damage, ESD or EOS plus preventative maintenance. Including a 5 day turnaround time and priority access to customer support
C3	Calibration service 3 years. Includes traceable calibration or functional verification where applicable, for recommended calibrations. Coverage includes the initial calibration plus 2 years calibration coverage.
C5	Calibration service 5 years. Includes traceable calibration or functional verification where applicable, for recommended calibrations. Coverage includes the initial calibration plus 4 years calibration coverage.
D1	Calibration data report
D3	Calibration data report 3 years (with option C3)
D5	Calibration data report 5 years (with option C5)

Ordering information post purchase

The 2 Series products offer many options to easily add functionality after the initial purchase.

Bandwidth upgrades after purchase

The analog bandwidth of the 2 Series MSO can be upgraded after the initial purchase. Bandwidth upgrades are purchased based on the current bandwidth and the desired bandwidth. All bandwidth upgrades can be performed in the field by installing a license.

Supported model	Bandwidth option	Bandwidth before upgrade	Bandwidth after upgrade
MSO22	SUP2-BW70T100-2	70 MHz	100 MHz
	SUP2-BW70T200-2	70 MHz	200 MHz
	SUP2-BW70T350-2	70 MHz	350 MHz
	SUP2-BW70T500-2	70 MHz	500 MHz
	SUP2-BW100T200-2	100 MHz	200 MHz
	SUP2-BW100T350-2	100 MHz	350 MHz
	SUP2-BW100T500-2	100 MHz	500 MHz
	SUP2-BW200T350-2	200 MHz	350 MHz
	SUP2-BW200T500-2	200 MHz	500 MHz
	SUP2-BW350T500-2	350 MHz	500 MHz
MSO24	SUP2-BW70T100-4	70 MHz	100 MHz
	SUP2-BW70T200-4	70 MHz	200 MHz
	SUP2-BW70T350-4	70 MHz	350 MHz
	SUP2-BW70T500-4	70 MHz	500 MHz
	SUP2-BW100T200-4	100 MHz	200 MHz
	SUP2-BW100T350-4	100 MHz	350 MHz
	SUP2-BW100T500-4	100 MHz	500 MHz
	SUP2-BW200T350-4	200 MHz	350 MHz
	SUP2-BW200T500-4	200 MHz	500 MHz
	SUP2-BW350T500-4	350 MHz	500 MHz

Instrument functionality upgrade with an option bundle

Choose from option bundles with different levels of functionality to suit your application needs.

Feature	Description
2-MSO	Add MSO function with 16 digital channels; includes P6316 digital probe and accessories
2-SOURCE	Arbitrary function generator (AFG), digital pattern generator (DPG), and frequency response analysis (Bode plot)
2-SERIAL	I ² C, SPI, UART, CAN, CAN-FD, SENT, LIN serial trigger and analysis
2-ULTIMATE	Includes 2-SOURCE and 2-SERIAL

Additional software for extended functionality

Purchase additional software with flexible licensing to extend the capabilities of your instrument for collaboration and offline analysis. Option bundles with different levels of functionality are being offered to suit different application needs. Each of these bundles can be purchased as a 1-year subscription or as a perpetual license.

Software option	Description
TEKSCOPE-STARTER	TekScope PC software bundles for various applications
TEKSCOPE-PRO-AUTO	
TEKSCOPE-PRO-SR	
TEKSCOPE-PRO-PWR	
TEKSCOPE-PRO-MIL	
TEKSCOPE-ULTIMATE	
TEKDRIVE-STARTER	TekDrive software for T&M workspace collaboration
TEKDRIVE-PRO	
TEKDRIVE-ULTIMATE	
KICKSTART-SUITE	Kickstart instrument control and data analysis software
KICKSTART-AFG	
KICKSTART-DL	
KICKSTART-DMM	
KICKSTART-IVC	
KICKSTART-PS	
KICKSTART-SCOPE	
KICKSTART-HRMA2	
KICKSTART-ACT1/2/5	



Tektronix is ISO 14001:2015 and ISO 9001:2015 certified by DEKRA.

ASEAN / Australasia (65) 6356 3900
 Belgium 00800 2255 4835*
 Central East Europe and the Baltics +41 52 675 3777
 Finland +41 52 675 3777
 Hong Kong 400 820 5835
 Japan 81 (120) 441 046
 Middle East, Asia, and North Africa +41 52 675 3777
 People's Republic of China 400 820 5835
 Republic of Korea +82 2 565 1455
 Spain 00800 2255 4835*
 Taiwan 886 (2) 2656 6688

Austria 00800 2255 4835*
 Brazil +55 (11) 3759 7627
 Central Europe & Greece +41 52 675 3777
 France 00800 2255 4835*
 India 000 800 650 1835
 Luxembourg +41 52 675 3777
 The Netherlands 00800 2255 4835*
 Poland +41 52 675 3777
 Russia & CIS +7 (495) 6647564
 Sweden 00800 2255 4835*
 United Kingdom & Ireland 00800 2255 4835*

Balkans, Israel, South Africa and other ISE Countries +41 52 675 3777
 Canada 1 800 833 9200
 Denmark +45 80 88 1401
 Germany 00800 2255 4835*
 Italy 00800 2255 4835*
 Mexico, Central/South America & Caribbean 52 (55) 56 04 50 90
 Norway 800 16098
 Portugal 80 08 12370
 South Africa +41 52 675 3777
 Switzerland 00800 2255 4835*
 USA 1 800 833 9200

* European toll-free number. If not accessible, call: +41 52 675 3777

For Further Information. Tektronix maintains a comprehensive, constantly expanding collection of application notes, technical briefs and other resources to help engineers working on the cutting edge of technology. Please visit www.tek.com.

Copyright © Tektronix, Inc. All rights reserved. Tektronix products are covered by U.S. and foreign patents, issued and pending. Information in this publication supersedes that in all previously published material. Specification and price change privileges reserved. TEKTRONIX and TEK are registered trademarks of Tektronix, Inc. All other trade names referenced are the service marks, trademarks, or registered trademarks of their respective companies.

30 May 2023 48W-73857-5
tek.com

Tektronix[®]